

AZ 1512 – run sheet

Merck

[nanyte.com/photorelists/az-1512](https://www.merck.com/photorelists/az-1512) · last updated 2026-07-26

Thickness: 1.4–3.9 μm

Softbake: 90–110 °C · hotplate

Post-exposure bake: 105–115 °C

Develop: Developer AZ 400K or AZ 300MIF (tank immersion); AZ 917MIF (puddle) · Dilution AZ 400K 1:4; AZ 300MIF and AZ 917MIF used as supplied (both metal-ion-free/ready-to-use) · Time 60 s

Hardbake: 100–110 °C