

SU-8 2010 – run sheet

Kayaku Advanced Materials

nanyte.com/photoresists/su-8-2010 · last updated 2026-09-13

Thickness: 9.6–20.6 μm

Softbake: 95 °C · hotplate

Exposure dose – dose by film thickness

Film thickness	Dose
-----------------------	-------------

0.5–2 μm	60–180 mJ/cm^2
---------------------	--------------------------------

3–5 μm	90–105 mJ/cm^2
-------------------	--------------------------------

6–15 μm	110–140 mJ/cm^2
--------------------	---------------------------------

16–25 μm	140–150 mJ/cm^2
---------------------	---------------------------------

26–40 μm	150–160 mJ/cm^2
---------------------	---------------------------------

Post-exposure bake: 95 °C · hotplate

Develop: Developer SU-8 Developer; ethyl lactate or diacetone alcohol may also be used · Rinse Spray and wash the developed image with fresh SU-8 developer for about 10 s, then air-dry with filtered pressurised air or nitrogen. · Method immersion, spray or spray-puddle

Hardbake: 150–250 °C · 5–30 min